

Spacers & Standoffs





Hexagon Spacers								
F	C			F		С		
Width Across the Flats (± 1/64)	Clearance Hole			Width Across	Clearance Hole			
	Hole Number	Max	Min	the Flats (± 1/64)	Hole Number	Max	Min	
3/16	#1	.077	.067	3/8	#8	.176	.166	
3/16	#2	.100	.090	3/8	#10	.202	.192	
3/16	#4	.124	.114	1/2	#6	.150	.140	
1/4	#2	.100	.090	1/2	#8	.176	.166	
1/4	#4	.124	.114	1/2	#10	.202	.192	
1/4	#6	.150	.140	1/2	1/4	.262	.252	
1/4	#8	.176	.166	5/8	#6	.150	.140	
5/16	#4	.124	.114	5/8	#8	.176	.166	
5/16	#6	.150	.140	5/8	#10	.202	.192	
5/16	#8	.176	.166	5/8	#1/4	.262	.252	
5/16	#10	.202	.192	5/8	#5/16	.325	.315	
3/8	#6	.150	.140	5/8	#3/8	.390	.380	
							:	
Tolerance on Length (up to 4 in.)			Nylon parts: ±.015		All other materials: ±.005			

Description	A hexagonal, unthreaded, mechanical device used to hold two components at a given distance from each other.
Applications/ Advantages	Hex spacers are much less common than round, used in some applications to resist twisting. Aluminum is popular for its light weight/ strength compromise. It is non-magnetic, performs well in severe temperatures, and has insulating properties. Nylon is a good insulator and has a surface smoothness which will not fray the insulation of wires that rub against it. Brass is used in making high-quality spacers. It is conductive, resists corrosion, and is non-magnetic. It is costlier and heavier than aluminum and is usually plated zinc or nickel. Stainless has the advantages of brass but has superior resistance to corrosion and chemical fumes. Steel is used in applications requiring greater strength, but it is heavier than aluminum and does not resist corrosion like aluminum or brass.
Material	Aluminum: 2011 Aluminum (Copper: 5.0-6.0%; Silicon: 0.4% maximum; Iron: 0.7% maximum; Zinc: 0.3% maximum; Bismuth: 0.2-0.6%; Lead: 0.2-0.6%) Nylon: Nylon 6/6 Brass: C36000 Brass (Copper: 60.00-63.00%; Lead: 2.50-3.70%; Iron: .35% maximum) Stainless: 303 stainless, passivated to ASTM A 380 Steel: 12L14 Steel-Leaded Grade A (Carbon: .15% maximum; Manganese: .85-1.15%; Phosphorus: .0409%; Sulphur: .2635%)